

2-conductor through terminal block

Item No.: 283-901



2-conductor through terminal block

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	283-901
GTIN / EAN	4044918297615
Content	1
Order amount	20
Customer item number	

Notes



Technical data


Miscellaneous

Total number of connection points	2
Total number of potentials	1
Color	gray
Ratings according to 1	IEC/EN 60947-7-1
Pollution degree (1)	3
Rated voltage EN (1) [V]	800 [V]
Rated surge voltage (1) [kV]	8 [kV]
Nominal current [A]	76 [A]
Connection technology (1)	CAGE CLAMP®
Solid sizes 1	0.2 ... 16 mm ² / 24 ... 6 AWG

Technical data	
<i>Fine-stranded wires 1</i>	<i>0.2 ... 16 mm² / 24 ... 6 AWG</i>
<i>Strip length 1</i>	<i>16 ... 17 mm / 0.63 ... 0.67 in</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Design</i>	<i>horizontal</i>
<i>Marking level</i>	<i>Center marking</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Fire load [MJ]</i>	<i>0.536 [MJ]</i>
<i>Weight [g]</i>	<i>35.588 [g]</i>
<i>Width</i>	<i>12 mm / 0.472 in</i>
<i>Height from upper-edge of DIN-rail [mm]</i>	<i>37.5 [mm]</i>
<i>Height from upper-edge of DIN-rail</i>	<i>37.5 mm / 1.476 in</i>
<i>Length</i>	<i>94.5 mm / 3.72 in</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.