

Weller**100 Watt, 120v, 700°F Heavy Duty 3-wire Soldering Iron with CT6F7 Tip**

◀ previous print close next ▶▶

Product Details

Catalog No.	W100P3
UPC Code	037103474278
Type	Temperature Controlled
Wattage	100 W
Temperature Range	600° F/700° F/800° F
Cord Length	6 ft.
Components Supplied	CT6F7
Packaging	Industrial Box/Carton
Tech. Spec.	<u>Solder Safety Warnings.pdf</u>
Low Res. Image	<u>W100P3_100.jpg</u>
High Res. Image	<u>W100P3_300.jpg</u>
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- **Uses Weller "closed loop" method of controlling maximum tip temperature**
- **Portable line voltage iron - no base station required**
- **Stainless steel modular plug-in heater, greater efficiency & versatility**
- **Temperature is controlled by tip-600°F, 700°F, and 800°F tips available**
- **Nominal heat-up time with 700°F tip is 110 seconds**
- **Three-wire grounded cord set**
- **Uses CT series tips**
- **Heating element type: Nichrome wound, plug in**
- **UL and cUL listed**