



**Intermediate
T&B Catalog Number:**

TY125-40

UPC Number:

78621089551

Status:

Active

Description:

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 141.48mm (5.57 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), UL Recognized Tensile Strength Rating of 135 Newtons (30 Pounds), Military Specified (MIL-SPEC MS-3367-5), Bulk Pack

Features

The integrally formed nylon pawl combines low insertion and high locking strength.

Standards

UL Listed

General

Material Nylon 6.6
Color Natural

Dimension Information

Nominal Length (inches) 5
Length (inches) 5.6
Width (inches) 0.130
Max. Wire Bundle Diameter (inches) 1 1/4
Min. Wire Bundle Diameter (inches) 1/16

Specifications

Temperature Rating -40°F to 185°F
Flammability Rating UL 94 V-2

Tooling

Application Tools ERG50, QC-100, L-200, L-400-C

Packaging

T&B Order Multiple 1000
T&B Inner Pack 1000
Package in Units 10000
T&B Sold in UOM Each
T&B Weight Per UOM 1.25 lbs. per 1000

Certifications

RoHS Compliance Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com