

TY29M

## **Ty-Rap®**

Bulk - Standard Nylon 6/6 cable ties. Body width of 0.270 in. and a length of 30.00 in. Maximum wire bundle diameter 9 in.



### General

T&B Sales Drawings:	WSD-000280
Type:	Ty-Rap Cable Ties
MIL-SPEC:	MS3367-6
T&B UPC:	78621083067
T&B Status:	M
Colour:	Natural
Material:	Nylon 6/6

### Dimension Information

Temperature Range:	-40°F to 185°F (-40°C to 85°C)
Length:	30 in. / 762 mm