

Type B Liquidtight Tubing & Fittings
T&B Catalog Number:

LTC100-TB

UPC Number:

78621078956

Status:

Active

Description:

1 Inch Black Non-metallic Type B Industrial Grade Liquidtight Conduit

Features

Fast installation, even in tight or cramped spaces.

Smooth inner diameter allows easy wire pulling.

Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.

Lightweight and liquidtight.

Application

Machine tools, motor hookups, food processing equipment, extensions from wire ways, and sensor and micro switch wiring found in control consoles.

General

Material

PVC

Color

Black

Working Temperatures

-18 C to +105 C

Dimension Information

Size (inches)

1

I.D. - Minimum (inches)

1.041

I.D. - Maximum (inches)

1.066

O.D. - Minimum (inches)

1.29

O.D. - Maximum (inches)

1.315

Packaging

T&B Order Multiple

100

Package in Units

100

T&B Sold in UOM

Feet

T&B Weight Per UOM

30.31 lbs. per 100

Application Support

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications

Available on Website

Certifications

RoHS Compliance

Yes

Certifications

File Nbr:

E 95745

For further technical assistance, please contact us...Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.comT&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com