



Standard
T&B Catalog Number:

L-7-50-9-C

UPC Number:

72849491720

Status:

Active

Description:

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 188.85mm (7.435 Inches), Width of 4.73mm (0.186 Inches), Thickness of 1.35mm (0.053 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

General

Material	Nylon 6.6
Color	Natural

Dimension Information

Nominal Length (inches)	7
Length (inches)	7.5
Width (inches)	0.187
Max. Wire Bundle Diameter (inches)	1 3/4
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Military Standard Part No.	MS-3367-1-9
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, QC-100, L-200, L-400-C
-------------------	-------------------------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	10000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	5 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000222
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

