



# Einhell

## HOME

## TH-AP 650 E All Purpose Saw

Art.-No. 43.261.41

### Features

- Toolless saw blade change (1)
- Toolless adjustable sole plate (2) for optimal utilisation of the saw blade
- Electronic stroke rate control (3)
- Ergonomic, slim design with soft handle (4)

### Standard accessories

- Saw blade for metal (5)
- Saw blade for wood (6)




### Technical Data

- |                                      |                               |
|--------------------------------------|-------------------------------|
| ■ Mains:                             | 230 - 240 V ~ 50 Hz           |
| ■ Power:                             | 650 W                         |
| ■ Strokes:                           | 500 – 3,000 min <sup>-1</sup> |
| ■ Cutting depth max. (wood / metal): | 150 / 10 mm                   |
| ■ Saw blade thickness:               | 0.5 – 1.4 mm                  |
| ■ Stroke height:                     | 20 mm                         |
| ■ Product weight:                    | 2.8 kg                        |

### Logistic Data

- |                       |                   |
|-----------------------|-------------------|
| ■ Net weight:         | 2.9 kg            |
| ■ Gross weight:       | 3.2 kg            |
| ■ Packing dimensions: | 490 x 80 x 180 mm |
| ■ Bar code:           | 4006825 585292    |
| ■ Sales unit:         | 5 pcs             |



### As special accessory available:

**2 pcs saw blade set**

Art.-No.: 43.261.30

Bar code: 4006825 552225