



- Compact, 4-conductor KNX connectors with PUSH WIRE®
- Simple push-in termination for solid conductors
- 4-conductor entries allow devices to be replaced without disrupting the KNX bus connection

**Technical data:**

	IEC/EN 60664-1		
Ratings per	III	III	II
Overvoltage category	3	2	2
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	6 A	6 A	6 A
Approvals per	UL/CSA		
Use group UL 1059	B	C	D
Rated voltage	-	-	-
Nominal current UL	-	-	-
Nominal current CSA	-	-	-

**Conductor data:**

Connection technology	PUSH WIRE®
Conductor size: solid	4 x 0.6 ... 0.8 mm or 4 x 1.0 mm Ø
AWG	4 x 22 ... 20 "sol." or 4 x 18 "sol."
Strip length	5 ... 6 mm / 0.20 ... 0.24 in.

**Material data:**

Material group	I
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL 94	V0
Lower/Upper limit temperature	-60 °C / +105 °C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>cu</sub> )
Contact plating	tin-plated
