

LED Downlights



VT-8010

HIGHLIGHTS :

WATTS



12

EQ. WATTS



40

LUMINOUS



840

BEAM ANGLE



110

Item No	: VT-8010
SKU Code	: 4973
Watts	: 12
EQ Watts	: 40
Voltage	: 200-240V,50/60Hz
Lumen(lm)	: 840
Color Temperature	: 4000K
Beam Angle	: 110
Commercial type	: OVAL
PF	: >0.9
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP66
Body type	: PLASTIC CLAD ALUMINUM
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230629050
Unit size	: 290x200x100mm
Packing details	: 10
Unit cbm	: 0.00425

PRODUCT FEATURES

- Innumerable styles & Elegant appearance
- Non - Flickering
- No UV Radiation
- Premium Quality Power Driver with lowest power factor saver & high RA
- Varied finishes with strong die cast Aluminium body
- Residences, Showrooms, Hotels & Boutiques etc.

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES