



SDRW-08D2S-U

Harmony of Technology and Aesthetics

Burn disc with enhanced data protection in just 3 quick steps and intuitive Disc Encryption lets you do this easily.

- **Elegant appearance embody the harmonious marriage of technology and aesthetics**
- **Disc Encryption doubles the security with password-controlled and hidden-file functionality**
- **Drag-and-burn interface accomplishes entire jobs in three easy steps**

FEATURE



Disc Encryption

Double security on-the-go

Disc Encryption doubles the security with Password-controlled and hidden-file functionality.



Drag and Burn

3 easy steps to complete disc burning

Drag-and-burn interface accomplishes entire jobs In three easy steps.



ID Design

Bright and Dazzling Design

Elegant appearance embody the harmonious marriage of technology and aesthetics.



PACKAGE CONTENTS

- ASUS SDRW-08D2S-U Drive and drive stand
- USB Y Cable
- Bundle software: Cyberlink Power2Go v6
- Multi-Language Quick Installation Guide



SPECIFICATIONS

Color	<ul style="list-style-type: none"> • Black / White
Read Speed	<ul style="list-style-type: none"> • DVD±R:8X • DVD±RW:8X • DVD-ROM:8X • DVD±R(DL):8X • DVD-ROM(DL):8X • DVD-RAM:5X • CD-R/RW/ROM:24X • DVD video playback:4X • VCD playback:10X • Audio CD Playback:10X
Write Speed	<ul style="list-style-type: none"> • DVD±R:8X • DVD+RW:8X • DVD-RW:6X • DVD±R(DL):6X • DVD-RAM:5X • CD-R:24X • CD-RW:16X
Disc Formats	<ul style="list-style-type: none"> • Reading: DVD±R(SL/DL), DVD±RW, DVD-ROM(SL/DL), DVD-RAM, DVD Video, CD-R, CD-RW, CD-ROM, Audio CD, VCD, CD-I, CD-Extra, Photo CD, CD-text, CD-ROM/XA, Multi-session CD • Writing: DVD±R(SL/DL), DVD±RW, DVD-RAM, CD-R, CD-RW

Access Time (1/3 Stroke)	<ul style="list-style-type: none"> • DVD:160ms • CD:140ms
Interface	<ul style="list-style-type: none"> • USB 2.0
Data Buffer	<ul style="list-style-type: none"> • 1 MB
O/S Compatibility	<ul style="list-style-type: none"> • Windows® 7 / Vista / XP

Configurations

Mounting Orientation	<ul style="list-style-type: none"> • Horizontal (+5° ~ -5°)
Dimensions	<ul style="list-style-type: none"> • 157 x 142 x 21 mm(L/W/H)
Weight	<ul style="list-style-type: none"> • 313g (353g with stand)

Electrical and Environmental Specifications

Power Requirement	<ul style="list-style-type: none"> • USB Power +5V ± 5%
Temperature	<ul style="list-style-type: none"> • Operating: 5°C to 40°C • Storage: -30°C to 60°C
Humidity	<ul style="list-style-type: none"> • Operating:15%~80% (Non-condensing) • Storage:10%~90% (Non-condensing)

⊙ For more details, please contact the addresses below.

⊙ Specifications are subject to changes without notice. ⊙ All other brands and names are properties of their respective owners.