



Task Lamp XL

DN1190

If you need maximum light, look no further. This is a professional high power workstation lamp, lighting up wide areas on your desk, work station, drawing board or large painting.

The large shade can be smoothly adjusted vertically, horizontally and laterally to any desired position. With this great light you will be amazed how much better you will see the finer details, contrast and true colours in your work. The low heat full spectrum daylight™ light with 6,500°K improves contrast, reduces glare and is the best lighting available for colour rendering. The light has a dimming capability.



daylight™ LEDs



Eco friendly
uses 90% less
energy



Energy saving



Slim &
lightweight



naturalight™

Task Lamp XL

DN1190

Overview

- 84 Bright Daylight LEDs
- Brightness 3400 Lux at 30cm using only 21W of power
- Continuous Dimming to 10%
- Multi position head joint to direct light where needed
- Even spread of light for large area
- Shade width - 58 cm (22.5 inch)



Technical information

Packaging information

Item code	DN1190
Colour box width	745mm (29.33 in)
Colour box depth	120mm (4.72 in)
Colour box height	260mm (10.24 in)
Total packed weight	2.66kg (6 lbs)
Products per carton	4

Product information

Assembled Width	58cm (23 in)
Assembled Height	50cm (19½ in)
Assembled Depth	60cm (23½ in)
Assembled Weight	1.92kg (4 lbs)
Length of cable	1.75m
Main colour	White

Light output information

Light source type	LED
Total wattage	21w
Colour temperature	6500

Contact us

The Daylight Company Ltd
Info.uk@daylightcompany.com
UK + 44 (0)20 8964 1200
FR 0825 00 49 46
DE 0800 329 2667

