



Smart Lamp R10

DN1310

Why do we call this Lamp SMART

1. Full spectrum light for improved contrast when reading and color matching
2. It is dimmable, allowing you to set the light at the brightness level you require
3. It is portable, light weight and foldable so you can take it anywhere
4. It is USB compatible allowing you to plug into the AC Adapter (included) your computer or phone charger.



Smart Lamp R10

DN1310

Overview

- Rechargeable - up to 4 hours of light
- Daylight LEDs with 3 step dimmer
- 3 ways to power:
 - - Internal rechargeable battery (included)
 - - Plug in power supply
 - - USB Cable

Technical information

Packaging information

Item code	DN1310
Colour box width	80mm (3.15 in)
Colour box depth	80mm (3.15 in)
Colour box height	255mm (10.04 in)
Total packed weight	0.32kg (0½ lbs)
Products per carton	30

Product information

Assembled Width	20.0cm (8 in)
Assembled Height	25.0cm (10 in)
Assembled Depth	7.5cm (3 in)
Assembled Weight	0.246kg (0½ lbs)
Length of cable	1.5m
Main colour	White

Light output information

Light source type	LED
Total wattage	1.8w
Colour temperature	5500K-6500K

Batteries info

Battery types required	rechargeable batteries
------------------------	------------------------

Contact us

The Daylight Company Ltd
Info.uk@daylightcompany.com
UK + 44 (0)20 8964 1200
FR 0825 00 49 46
DE 0800 329 2667