

GateKeeper



Now with
High Resolution
1280 x 720P
recording

Low energy
1W LED
equivalent to
150W halogen
approx 40,000
hour life


OYN-X | GATEKEEPER

COMBINED SECURITY CAMERA LED FLOODLIGHT SYSTEM

FEATURES:

- DETECT THE INTRUDER
- FLOODLIGHT THE AREA
- INITIATE A VIDEO RECORDING
- DELIVER AN AUDIBLE WARNING

GateKeeper comes complete with:



4GB SD card and SD card reader
Fixing screws and Allen key
User Manual

SPECIFICATION


PIR detection angle 160 Deg and detection range up to 10M
Records 20 seconds image recording for image stream: 15fps at 1280X720P Pixels
Built in SD card slot for SD memory card
SD card slot for additional storage, max memory size up to 32G
SD card spec.: FAT16(SD)/ FAT32(SDHC)
Automatic exposure control, white bal
Auto Date & Time stamp
Effective viewing angle:40 deg
Effective viewing distance: 8M
Image format: JPEG AVI File
Rating AC 220V -240V ~50Hz
AC 11W COB LED
Auto light sensor
Sensitivity control
Timer control: 5 seconds - 7 minutes
Floodlight time delay control
IP Rating: IP55



Eco friendly
high intensity LED



PIR motion detector
with integral photocell



High resolution
digital camera



Time
control



Built in DVR records
directly to 4GB SD card



Easy replay on
Windows Media Player



Time and
date setting