

PIXMA MG2550S

A compact home All-In-One printer, scanner and copier that produces extraordinary results.

The perfect everyday All-In-One for printing, scanning and copying. From text-heavy documents to family photos, the compact Canon PIXMA MG2550S's print engine is built for quality and ease-of-use.



- Compact and affordable All-In-One colour printer, scanner and copier
- Prints documents and photos with ease
- Fast print speed of 8 ipm mono, 4 ipm colour
- Optional XL ink cartridges for improved economy
- Energy efficient Auto Power On/Off
- High-quality prints
- Get artistic with Canon's CREATIVE PARK PREMIUM software
- See memories come to life with the My Image Garden software

Product Range



PIXMA MG3050 Series



PIXMA MG2550S

PIXMA MG3050 Series
PIXMA MG2550S

Technical Specifications

GENERAL SPECIFICATIONS

Functions

Print, Copy, Scan

PRINTER SPECIFICATIONS

Print Resolution

Up to 4800^[1] x 600 dpi

Print Technology

2 FINE Cartridges (Black and Colour)

Mono Print Speed

Approx. 8.0 ipm^[2]

Colour Print Speed

Approx. 4.0 ipm^[2]

Two Sided Printing

Manual operation

CARTRIDGES AND YIELDS

Ink Efficient Series Cartridges

PG-545 (Black)

CL-546 (Colour)

Optional XL Ink Cartridges

PG-545XL (Black)

CL-546XL (Colour)

Cartridge Yield (Plain paper)

A4 colour documents printing^[3]

Black: 180 pages

Black XL: 400 pages

Colour: 180 pages

Colour XL: 300 pages

PAPER SUPPORT

Paper Types

Plain Paper

Envelopes

Photo Paper Plus Glossy II (PP-201)

Photo Paper Glossy "Everyday Use" (GP-501)

Rear tray: Max. 60 sheets (plain paper)

Maximum Paper Input

Paper Sizes

A4, A5, B5, 10x15cm, 13x18cm, Envelopes (DL, COM10), Letter, Legal

Paper Weight

Plain paper: 64 - 105 g/m²

Canon photo paper: up to 275 g/m²

SCANNER SPECIFICATIONS

Scanner Type

CIS flatbed photo and document scanner

Scanner Resolution (Optical)

600 x 1200 dpi^[4]

A4 Scan Speed

Approx. 14 seconds^[5]

Scanning Depth (Input / Output)

Colour: 48 bit / 24 bit

Greyscale: 16 bit / 8 bit

Maximum Document Size

216 x 297 mm

COPIER SPECIFICATIONS

Copy Speed

sFCOT: Approx. 31 seconds^[6]

sESAT: Approx. 1.6 ipm^[6]

Multiple Copy

21 copies (max.)

Copy Functions

Document copying (plain paper)

INTERFACE

Display Type & Size

No display

Interface Type - PC / Mac

Hi-Speed USB (B Port)

SOFTWARE

Supported Operating Systems

Windows 10

Windows 8.1 (including Windows 8.1 Update), Windows 8

Windows 7, Windows 7 SP1

Windows Vista SP2

Windows XP SP3 (32 bit only)

Note: For Windows, .NET Framework 4 or .NET Framework 4.5 is required.

For Windows XP, XPS Essentials Pack is required.

Mac OS X v10.7.5 to Mac OS X v10.11

Minimum System Requirements

Windows: 3.1GB disk space, Internet Explorer 8
Mac: Internet connection, 1.5GB disk space, Safari 5
Display: 1024 x 768 XGA

Software Included

MP Driver including Scanning Utility
My Image Garden with Full HD Movie Print^[7]
Quick Menu
Easy-WebPrint EX (download)^[8]

PHYSICAL FEATURES

Weight

Approx. 3.5 kg

Dimensions (W x D x H)

426 x 306 x 145 mm

Operating Temperature

5 - 35°C

Operating Humidity

10-90%RH (no dew condensation)

Power Source

AC 100-240V, 50/60Hz

Power Consumption

Off: Approx. 0.4 W

Standby (connected to PC via USB): Approx. 1.0 W (scanning lamp off)

Standby (all ports connected): Approx. 1.0 W (scanning lamp off)

Time to enter Standby mode: 7 minutes

Copying: Approx. 9 W^[9]

Footnotes

^[1] Ink droplets can be placed with a minimum pitch of 1/4800 inch

^[2] A4 document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.

^[3] Declared yield value in accordance with ISO/IEC 24711 standard. Values obtained by continuous printing.

^[4] Optical resolution is a measure of maximum hardware sampling resolution based on ISO 14473 standard. When scanning in high resolution, the maximum scan size is restricted.

^[5] Color document scan speed is measured with ISO/IEC 29183 Target A. Scan speed indicates the time measured between pressing the scan button of the scanner driver and the on-screen status display turns off.

Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.

^[6] Colour document copy speed is measured based on average of sFCOT and sESAT in Performance Test of ISO/IEC 29183 standard.

^[7] Full HD Movie Print is available for MOV and MP4 movie files created by select Canon digital cameras and camcorders. Requires installation of software bundled with Canon video or digital camera, from which the movie was captured. MOV files require: ZoomBrowser EX / ImageBrowser (version 6.5 or later), MP4 files require: ImageBrowser EX (version 1.0 or later).

^[8] Easy-WebPrint EX requires Internet Explorer 8 or later

^[9] When copying ISO/JIS-SCID N2 (printed by inkjet printer) on A4 size plain paper using default settings.

Standard disclaimers

All specifications subject to change without notice.

Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc.

Ink yield may vary depending on texts/photos printed, applications software used, print mode and type of paper used. For yield information see www.canon-europe.com/ink/yield

Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.

Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time.

All brand and product names are trademarks of their respective companies.

PIXMA MG2550S

A compact home All-In-One printer, scanner and copier that produces extraordinary results.

The perfect everyday All-In-One for printing, scanning and copying. From text-heavy documents to family photos, the compact Canon PIXMA MG2550S's print engine is built for quality and ease-of-use.



Sales Start Date: September 2016

Product Details:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PIXMA MG2550S EUR	0727C006BA	4549292072372	<Please fill in RRP>

Ink Consumables:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PG-545	8287B001AA	4960999974507	<Please fill in RRP>
CL-546	8289B001AA	4960999974521	<Please fill in RRP>

Optional Ink Consumables:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PG-545XL	8286B001AA	4960999974491	<Please fill in RRP>
CL-546XL	8288B001AA	4960999974514	<Please fill in RRP>
PG-545/CL-546 MULTI BL	8287B005AA	8714574605517	<Please fill in RRP>
CRG PG-545XL/CL-546XL PHOTO VALUE BL	8286B006AA	8714574630793	<Please fill in RRP>

Measurement / Logistic Information:

Product Name	Mercury Code	Pack type	Pack description	Quantity per pack	Length (mm)	Width (mm)	Height (mm)	Net Weight (kg)	Gross Weight (kg)
PIXMA MG2550S EUR	0727C006BA	EA	Each	1	480.1	192.8	371.2	3.2	4.5
		CT	Carton	24	1159.8	963.2	743.4	108	110.6
		EP	Euro Pallet	36	1159.8	963.2	1117.6	162	164.6

What's in the box?

- All-In-One printer – Canon PIXMA MG2550S
- FINE Cartridges
- Power cord
- Setup CD-ROM (CD only for Windows – Mac drivers available online)
- Manuals and other documents

The Canon logo is displayed in its signature red color with a white outline, positioned in the bottom right corner of the page.