

15vdc 3.34A 50W Desktop Power Supply

PowerPax



This switch mode power supply is rated to 50W maximum, providing a regulated 15vdc output at up to 3.34A with no minimum load. The unit meets latest CoC Tier 1 / Level VI efficiency standards and will be uprated to CoC Tier 2 requirements before the requirement is made mandatory. This power supply carries full safety approvals. Short circuit and over current protection is integral.


Part Numbers	SW4323B	Power Consumption (no load)	0.21W max
Output	15vdc 3.34A max. (No min. load)	Input Current (RMS Max.)	1.2A max
Power	50 Watts	Hi-Pot Spec	3000Vac 10mA 1 min. (I.P. to O.P.)
Line Reg	+/-5% at rated load	Output cable	1.5 Metres 18AWG 2468
Total Output Regulation	+/-5% at 0—100% load	Operating Temperature	0 to 40 degrees C
Ripple & Noise (mV p-p)	150mV	Storage Temperature	-20 to 80 degrees C
Protections	Over Current, Short Circuit and Over Voltage	Operating Humidity	10% to 90%
Case Size	Page2	Safety Approvals	UL, CUL, CB, CE, PSE, FCC, RCM
DC Plug	2.1 x 5.5 x 12mm	EMC Standards	EN55022:2010 Class B / FCC Part B
Polarity	+ve Centre	MTBF	50K Hours at 25 degrees C
Rated Input Voltage	100-240Vac	MTBF	50K Hours at 25 degrees C
Full Input Voltage Range	90-264Vac	Plastic Case	UL94V-0
Rated Frequency	50-60Hz		
Full Frequency Range	47-63Hz		
Efficiency	Level VI (88% average)		

Full spec sheet on this PSU is available on request. PowerPax Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice



15vdc 3.34A 50W Desktop Power Supply

PowerPax



PowerPax
www.powerpax.co.uk

AC ADAPTER
P/N : SW4323B
MODEL
INPUT(輸入): 100-240V~50-60Hz 1.2A MAX.
OUTPUT(輸出): 15V --- 3.34A **LPS**

For use with information technology equipment only
Laitte on liitettävä suojakoskettimilla varustettuun pistorasiaan
Apparaten må tilkoples jordat stikkontakt
Apparaten skall anslutas till jordat uttag

FOR INDOOR USE ONLY

EFFICIENCY LEVEL **VII**

CE FC GS

LISTED I.T.E. POWER SUPPLY 60JJ

Energy Verified Rendement Énergétique Vérifié

RoHS

JET
IP:AC 100-240V 50/60Hz 95VA-120VA 1.2A
O/P:DC 15V/3.34A 必ず接続確認を行ってください

D/C:1535
MADE IN CHINA
ID NO. X
XXX

Full spec sheet on this PSU is available on request. PowerPax Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice

