

5000 Series - Standard
8000 Series - ESD

DORAL SERIES



DIMENSIONS

SEAT
18" W x 17 H
2 3/4" Thick

BACK
16" W x 10 H
2" Thick

UPHOLSTERY OPTIONS

STANDARD



ESD



BUILT TO ORDER

Each chair is configured to your exact specifications – choice of arms, tilt, height range, base style, and glides/caster options.



Height Range	Base Style	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model #	ESD Model #
DESK	23" Black Nylon	17" - 22"	2 Way	-	5000	-
			3 Way	-	5001	-
			4 Way	-	5002	-
	25" Polished Aluminum	15 1/2" - 21"	2 Way	-	5050	8050
			3 Way	-	5051	8051
			4 Way	-	5052	8052
MID	27" Black Nylon	20 1/2" - 28"	2 Way	18" Adj. Chrome	5300	-
			3 Way	18" Adj. Chrome	5301	-
			4 Way	18" Adj. Chrome	5302	-
	27" Polished Aluminum	19" - 26 1/2"	2 Way	18" Adj. Chrome	5350	8350
			3 Way	18" Adj. Chrome	5351	8351
			4 Way	18" Adj. Chrome	5352	8352
	22" Black Tubular Steel	20" - 25"	2 Way	19" Welded Chrome	5200	-
			3 Way	19" Welded Chrome	5201	-
			4 Way	19" Welded Chrome	5202	-
	22" Chrome Tubular Steel	20" - 25"	2 Way	19" Welded Chrome	5210	8210
			3 Way	19" Welded Chrome	5211	8211
			4 Way	19" Welded Chrome	5212	8212
TALL	27" Black Nylon	23" - 33"	2 Way	18" Adj. Chrome	5500	-
			3 Way	18" Adj. Chrome	5501	-
			4 Way	18" Adj. Chrome	5502	-
	27" Polished Aluminum	21 1/2" - 31 1/2"	2 Way	18" Adj. Chrome	5550	8550
			3 Way	18" Adj. Chrome	5551	8551
			4 Way	18" Adj. Chrome	5552	8552
	22" Black Tubular Steel	25" - 30"	2 Way	19" Welded Chrome	5600	-
			3 Way	19" Welded Chrome	5601	-
			4 Way	19" Welded Chrome	5602	-
	22" Chrome Tubular Steel	25" - 30"	2 Way	19" Welded Chrome	5610	8610
			3 Way	19" Welded Chrome	5611	8611
			4 Way	19" Welded Chrome	5612	8612



ACCESSORIES

ARMS



A5

Standard Models



A8

ESD Models

CASTERS

Casters add 1" to seat height range.



HARD FLOOR CASTERS

Standard:
5-star: 3850S/5
Tubular: CADS/5
ESD: CARD5S



CARPET CASTERS

Standard:
5-star: 3850/5
Tubular: CAD/5
ESD: CAPD5S



SPECIALTY CASTERS

INTERVAL BRAKING
Standard: IBCS
ESD: IBCS-ESD

REVERSE BRAKING
Standard: RBCS
ESD: RBCS-ESD