



# CorePro LEDlinear MV

## CorePro LED linear R7S 118mm 14-100W 840 D

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light just like a halogen lamp. The deep dimming function enables a cozy ambience when using a dimmable fixture.


### Product data

General Information		Starting Time (Nom)	
Cap-Base	R7S [ R7s]		0.5 s
Bulb Shape	Linear	Warm Up Time To 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	15000 h	Power Factor (Nom)	0.8
Switching Cycle	50000X	Voltage (Nom)	220-240 V
Technical Type	14-100W		
Light Technical		Temperature	
Color Code	840 [ CCT of 4000K (841)]	T-Case Maximum (Nom)	90 °C
Luminous Flux (Nom)	1800 lm		
Luminous Flux (Rated) (Nom)	1800 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	128.57 lm/W	Approval and Application	
Color Consistency	<6	Energy Saving Product	Yes
Color Rendering Index (Nom)	80	Suitable For Accent Lighting	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Label (EEL)	A++
		Energy Consumption kWh/1000 h	14 kWh
Operating and Electrical		Product Data	
Input Frequency	50 to 60 Hz	Full product code	871869657881000
Power (Rated) (Nom)	14 W	Order product name	CorePro LED linear R7S 118mm 14-100W 840 D
Lamp Current (Nom)	74 mA	EAN/UPC - Product	8718696578810
Wattage Equivalent	100 W	Order code	929001243802
		Numerator - Quantity Per Pack	1

## CorePro LEDlinear MV

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001243802
Net Weight (Piece)	0.095 kg

### Dimensional drawing




Linear 220V 15W-100W1500lm 4000K R7S Dim

Product	D	C
CorePro LED linear R7S 118mm 14-100W 840 D	29 mm	118 mm

Photometric data

General Uniform Lighting



2016-07-13

