



MASTER LEDcandle DiamondSpark

MASTER LEDcandle DT 6-40W E14 B38 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data


| General Information | | Operating and Electrical | |
|--------------------------------------|-----------------|--|----------|
| Cap base | E14 [E14] | Luminous efficacy (rated) (nom.) | 75 lm/W |
| Bulb shape | B38 | Colour consistency | <6 |
| Nominal lifetime (nom.) | 25000 h | Color rendering index (nom.) | 80 |
| Switching cycle | 50000X | LLMF at end of nominal lifetime (nom.) | 70 % |
| Technical type | 6-40W | | |
| Light Technical | | Input frequency | 50-60 Hz |
| Luminous flux (nom.) | 470 lm | Power (Rated) (Nom) | 6 W |
| Luminous flux (rated) (nom.) | 470 lm | Lamp current (nom.) | 35 mA |
| Colour designation | Warm white (WW) | Wattage equivalent | 40 W |
| Correlated colour temperature (nom.) | 2200-2700 K | Starting time (nom.) | 0.5 s |
| | | Power factor (nom.) | 0.7 |

MASTER LEDcandle DiamondSpark

| | |
|---------------------------------|------------|
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case maximum (nom.) | 95 °C |
| Controls and Dimming | |
| Dimmable | yes |
| Mechanical and Housing | |
| Bulb finish | Clear (CL) |
| Approval and Application | |
| Suitable for accent lighting | No |
| Energy efficiency label (EEL) | A+ |

| | |
|---------------------------------|--------------------------------------|
| Energy Consumption kWh/1000 h | 6 kWh |
| Product Data | |
| Full product code | 871869645350600 |
| Order product name | MASTER LEDcandle DT 6-40W E14 B38 CL |
| EAN/UPC – product | 8718696453506 |
| Order code | 45350600 |
| Local Code | MLED6WCANDT14 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 10 |
| Material no. (12NC) | 929001140402 |
| Net weight (piece) | 0.063 kg |

Dimensional drawing



| Product | D | C |
|--------------------------------------|-------|--------|
| MASTER LEDcandle DT 6-40W E14 B38 CL | 38 mm | 113 mm |

LED DT 6-40W E14 2200-2700K B38 CL

