

MASTER LEDcandle

MASTER LEDcandle DT 6-40W B15 B38 CL



Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps come in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data

• General Information

Cap-Base	B15 [B15]
Reddot Design Award Winner mark	Reddot Design Award Winner 2016
Bulb Shape	B38
Nominal Lifetime (Nom)	25000 h
Switching Cycle B50L70	50000X 25000 h
Technical Type	6-40W

• Light Technical

Color Code	822-827 [tunable warm white]
Luminous Flux (Nom)	470 lm
Luminous Flux (Rated) (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature Setting(s)	2200-2700 K
Luminous Efficacy (rated) (Nom)	78.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

• Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	6 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V

• Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------

• Controls and Dimming

Dimmable	Yes
----------	-----

PHILIPS

MASTER LEDcandle

• Mechanical and Housing

Bulb Finish Clear


• Approval and Application

Energy Saving Product Yes
Suitable For Accent Lighting No
Energy Efficiency Label (EEL) A+
Energy Consumption 6 kWh
kWh/1000 h

• Product Data

Full product code 871869655601600
Order product name MASTER LEDcandle DT 6-40W B15 B38 CL
EAN/UPC - Product 8718696556016
Order code 929001140302
Numerator - Quantity Per Pack 1
Numerator - Packs per outer box 10
Material Nr. (12NC) 929001140302
Net Weight (Piece) 0.063 kg



Dimensional drawing



Candle B38 220-240V 6W-40W 2700K B15 D

Product	C	D
MASTER LEDcandle DT 6-40W B15 B38 CL	113 mm	38 mm

General Uniform Lighting



© 2016 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, October 29
data subject to change