



Supplied standard with all hoods and bases.  
Special sizes/hood combinations available.



Style may vary depending on size.



Standard European style – can be specified/supplied with hoods and bases.

### Metric PG-to-NPT Thread Adapters

| CAT. NO. | NPT THREAD (MATING) | THREAD (AT HOUSING) |
|----------|---------------------|---------------------|
| PG11-38  | 3/8"                | PG11                |
| PG16-50  | 1/2"                | PG16                |
| PG21-75  | 3/4"                | PG21                |
| PG29-100 | 1"                  | PG29                |
| PG36-125 | 1 1/4"              | PG29                |
| PG36-125 | 1 1/4"              | PG36                |
| PG36-150 | 1 1/2"              | PG36                |
| PG42-200 | 2"                  | PG42                |

### Metric ISO-to-NPT Thread Adapters

| CAT. NO. | NPT THREAD (MATING) | THREAD (AT HOUSING) |
|----------|---------------------|---------------------|
| M20-38   | 3/8"                | M20                 |
| M20-50   | 1/2"                | M20                 |
| M20-75   | 3/4"                | M20                 |
| M32-100  | 1"                  | M32                 |
| M32-125  | 1 1/4"              | M32                 |
| M40-125  | 1 1/4"              | M40                 |
| M40-150  | 1 1/2"              | M40                 |

### Metric Two-Screw Clamp Connectors

| CAT. NO.  | CABLE O.D. (IN.) |       | THREAD (AT HOUSING) |
|-----------|------------------|-------|---------------------|
|           | MIN.             | MAX.  |                     |
| CC11-38   | .400"            | .470" | PG11                |
| CC11-38P* | .250"            | .325" | PG11                |
| CC135-50  | .400"            | .535" | PG13.5              |
| CC16-50   | .455"            | .625" | PG16                |
| CC21-75   | .513"            | .815" | PG21                |
| CC21-100  | .800"            | .175" | PG291               |
| CC36-125  | 1.050"           | .450" | PG361               |
| CC42-150  | 1.500"           | .800" | PG421               |

\* Plastic

### Metric Cord Grip Connectors

| CAT. NO.  | CABLE O.D. (IN.) |       | THREAD (AT HOUSING) |
|-----------|------------------|-------|---------------------|
|           | MIN.             | MAX.  |                     |
| CG11-38   | .200"            | .470" | PG11                |
| CG11-38P* | .325"            | .340" | PG11                |
| CG135-50  | .285"            | .545" | PG13.5              |
| CG16-50   | .285"            | .625" | PG16                |
| CG21-75   | .395"            | .790" | PG21                |
| CG29-100  | .780"            | .060" | PG291               |
| CG36-125  | .780"            | .060" | PG291               |
| CG42-150  | 1.500"           | .800" | PG421               |

\* Plastic