



Puzzi 8/1 C

Spray extraction cleaner for upholstery and spot cleaning.

1 Lightweight

3 Convenient handling and good accessibility

2 Compact design

■ The Puzzi 8/1 C is ideal for cleaning upholstery and vehicle interiors.



Puzzi 8/1 C

- Foldable cable hook
- Convenient foot switch
- On-board storage for hand nozzle

Technical data

| | | |
|------------------------------------|-------------------|-----------------|
| Order Number | 1.100-227.0 | |
| EAN code | 4039784972360 | |
| Max. area performance | m ² /h | 12-18 |
| Air flow | l/s | 61 |
| Vacuum | mbar / kPa | 230 / 23 |
| Spray rate | l/min | 1 |
| Spray pressure/ram pressure | bar | 1 |
| Fresh / waste water tank | l | 8 / 7 |
| Power rating fan | W | 1200 |
| Power rating, pump | W | 40 |
| Weight | kg | 9,8 |
| Dimensions (L x W x H) | mm | 530 × 330 × 440 |
| Voltage | V | 220-240 |
| Frequency | Hz | 50-60 |

Equipment

| | | |
|--|---|-----|
| Spray hose with integral water feed | m | 2,5 |
| Integral accessory holder for hand tool | ■ | |
| Power cable | m | 7,5 |
| Upholstery nozzle | ■ | |
| Hand tool | ■ | |
| Cable hook | ■ | |

■ Included in delivery.

ACCESSORIES FOR PUZZI 8/1 C

1.100-227.0



| | | Order Number | Quantity | ID | Width | Length | Price | Description | |
|-------------------------------|----|--------------|------------|-------|--------|--------|-------|-------------|-------------------------------------|
| Hand tools | | | | | | | | | |
| | 1 | 4.130-001.0 | 1 piece(s) | ID 32 | 110 mm | | | | <input checked="" type="checkbox"/> |
| Spray-extraction hoses | | | | | | | | | |
| | 2 | 6.394-826.0 | 1 piece(s) | ID 32 | | 2.5 m | | | <input checked="" type="checkbox"/> |
| | 3 | 6.394-375.0 | 1 piece(s) | ID 32 | | 4 m | | | <input type="checkbox"/> |
| Floor tools | | | | | | | | | |
| | 4 | 4.130-007.0 | 1 piece(s) | ID 32 | 240 mm | | | | <input type="checkbox"/> |
| | 5 | 4.130-008.0 | 1 piece(s) | ID 32 | 240 mm | | | | <input type="checkbox"/> |
| Hard surface adapters | | | | | | | | | |
| | 6 | 4.762-014.0 | 1 piece(s) | | 240 mm | | | | <input type="checkbox"/> |
| Sonstiges | | | | | | | | | |
| | 7 | 4.006-907.0 | 1 piece(s) | ID 32 | | | | | <input type="checkbox"/> |
| | 8 | 4.025-004.0 | 1 piece(s) | ID 32 | 780 mm | | | | <input type="checkbox"/> |
| | 9 | 4.130-010.0 | 1 piece(s) | ID 32 | | | | | <input type="checkbox"/> |
| | 10 | 4.321-001.0 | 1 piece(s) | | | | | | <input type="checkbox"/> |

■ Included in delivery. □ Available accessories.