

# Alnico rectangular bar magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Max. operating temperature 220°C
- Mild steel pot, aluminium spacer.
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available
- Sold in pairs. North pole is indicated by a notch/dimple



## Product Information

Product No.	Eclipse Magnetics Product No.	Material	Length*	Width <i>mm</i>	Height	Weight / pair <i>kg</i>	Gauss
TL16131	E844	Alnico 5	20	10	5	0.030	1100
TL16132	E845	"	40	12.5	5	0.040	1100
TL16133	E846	"	60	15	5	0.130	1100

\*magnetic axis