



Datasheet for part number DBMN25PNK87

|   |
|---|
| Our Catalog Part Number: DBMN-25P-N-K87                               |
| Our Global Manufacturing Part Number: 053513-3243                     |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M |

| Product Datasheet               |   |
|---------------------------------|---|
| General                         | D*M High reliable D-Sub Connectors                |
| Wire Gauge Range AWG            | AWG 20-28   |
| Mating Cycles                   | 200   |
| Contact Arrangement             | 25 contacts size 20                               |
| Dielectric Withstanding Voltage | 1000 VAC at sea level                             |
| Current Rating                  | 7.5 A max   |
| Contact Resistance              | 7.5 milli Ohm max                                 |
| Operating Temperature           | -55°/+125°  |
| Salt Spray Test                 | 20 hours  |
| Shell Material                  | steel   |
| Shell Finish                    | pure tin over nickel                              |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                  |
| Insulator Color                 | black   |
| Gender                          | Pin   |
| Contact Type                    | Straight PCB                                      |
| Contact Material                | copper alloy                                      |
| Contact Finish                  | gold over nickel                                  |
| Hardware                        | .300" (7.6mm) Standoff, 4-40 Screwlock, Boardlock |