

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901310138

Status:

Active

Overview:

C-Grid III™

Description:

2.54mm Pitch C-Grid III™ Header, Dual Row, Vertical, 36 Circuits, Tin (Sn) Plating

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

General

Product Family

PCB Headers

Series

90131

Application

Signal, Wire-to-Board

Overview

C-Grid III™

Product Name

C-Grid III™

UPC

800753704343

Physical

Breakaway

Yes

Circuits (Loaded)

36

Circuits (maximum)

36

Color - Resin

Black

First Mate / Last Break

No

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polyester

Net Weight

2.196/g

Number of Rows

2

Orientation

Vertical

PC Tail Length

2.90mm

PCB Locator

No

PCB Retention

None

Packaging Type

Tray

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

Yes

Temperature Range - Operating

-55°C to +125°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

3.0A

Voltage - Maximum

350V

Solder Process Data

Lead-freeProcess Capability


WAVE

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-90131-001, SDA-90131



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

90131 Series

This document was generated on 08/31/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION