

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470027](#)  
**Status:** **Active**  
**Overview:** Watertite® Wet-Location Wiring Solutions  
**Description:** Watertite® Plug with Locking Blade, 3 Pole/4 Wire, NEMA L15-20, 3Ø 250V, Cord Grip Body Size F3

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130147</a>
IP Rating	IP67
NEMA Configuration	NEMA L15-20
Overview	<a href="#">Watertite® Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-8067
Product Name	Watertite®
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678871214
Woodhead	Yes

**Physical**

Cord Grip Body Size	F3 3/4"
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Net Weight	233.840/g
Poles	3-pole/4-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	3Ø 250V

**Material Info**

Old Part Number	26W75
-----------------	-------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

**Search Parts in this Series**

[130147 Series](#)