

General Information

Extended Product Type:	CPT 316
Product ID:	2CMA179280R1000
EAN:	7392696792806
Catalog Description:	Plug for extra low voltage, 16A, IP44, 3-pole
Long Description:	Plug Extra low voltage, rated current 16A, IP44 splashproof, 3-poles, frequency 50-60 Hz, color code Purple

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets for Extra Low Voltage » Plugs

Ordering

EAN:	7392696792806
Minimum Order Quantity:	10 piece
Country of Origin:	Germany (DE)

Dimensions

Product Net Width:	62 mm
Product Net Height:	62 mm
Product Net Length:	145 mm
Product Net Depth:	62 mm
Product Net Weight:	0.15 kg

Container Information

Package Level 1 Width:	136 mm
Package Level 1 Length:	337 mm
Package Level 1 Height:	137 mm
Package Level 1 Gross Weight:	0.15 kg
Package Level 1 EAN:	7392696792806
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q4
--------------	---

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry ,conduit(included)
Color:	Purple
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Extra low voltage plug
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#CPT 316
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	CPT
Product Name:	Industrial Plug
Protection Type:	Splashproof
Rated Current (I _n):	16 A
Rated Voltage (U _r):	20 ... 25 V
RoHS Date:	L23
Standards:	IEC 60 309-1, -2
Suitable For:	Plugs
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2416054

UNSPSC: 39120000

