

904-00686

Article Number: 904-00686

Description: Rack Mount Fiber Enclosure-Unloaded, Accepts 3 LGX Adapter Panels, 1U, BK, 1/pkg



Base Data	Local Order Number	FERM1U
	Type	FERM1U
	Color	Black (BK)
	Features and Benefits	<ul style="list-style-type: none"> • Removable front and rear covers provide easy access to cables. • Slide-out tray with easy-to-grip raised edge. • Cable management spools for effective slack management. • Optional splice trays to assist with cable splicing. • Panel positioning for easier patch cords access. • Round edge plastic fiber saddles for easier patch-cord routing. • Meet ANSI/TIA/EIA 568-C standards.
	Quantity Per	box
	Product Description	HellermannTyton rack mount enclosures are durable and support up to 1728 fibers. Rack enclosures work with standard 19" and 23" equipment racks and are designed to work with standard LGX adapter panels. HellermannTyton offers standard and GSA compliant rack mount enclosures. GSA compliant enclosures meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government projects.
	Technical Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 3 Adapter Panels, 1U, BK
	Short Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 3 LGX Adapter Panels, 1U, BK, 1/pkg
	Product Dimensions	Length L (Imperial)
Length L (Metric)		355.6mm
Width W (Imperial)		17.0"
Width W (Metric)		431.8mm
Height H (Imperial)		1.75"
Height H (Metric)		44.5mm
Material and Specifications		Material
	Material Shortcut	MET

904-00686



Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8538907080