

855-04208

Article Number: 855-04208



Description: Wall Mount Fiber Enclosure - Unloaded, accepts 4 Adapter Panels, 2 Splice Trays, Black, 1/pkg

Base Data	Local Order Number	FEWM24
	Type	FEWM24
	Color	Black (BK)
	Features and Benefits	<ul style="list-style-type: none"> • Durable stainless steel construction for long life. • Cable management spools for effective slack management. • Bend radius control to minimize hand and wrist strain. • Smooth grommet entry to protect cables from damage. • Locking tab for added security. • Meet ANSI/TIA/EIA 568-C standards.
	Quantity Per	box
	Product Description	To effectively manage optical fiber terminations and splices, HellermannTyton offers a line of wall mount enclosures. They provide a termination solution for LAN applications requiring fully enclosed wall mount enclosures. This product is designed to support up to four modular adapter panels, providing the flexibility to have up to 36 fibers when fully loaded. This enclosure houses two splice trays.
	Technical Description	Wall Mount Fiber Enclosure - Unloaded, accepts 4 Adapter Panels, 2 Splice Trays, Black
	Short Description	Wall Mount Fiber Enclosure - Unloaded, accepts 4 Adapter Panels, 2 Splice Trays, Black, 1/pkg
	Product Dimensions	Length L (Imperial)
Length L (Metric)		88.9mm
Width W (Imperial)		15.0"
Width W (Metric)		381.0mm
Height H (Imperial)		15.63"
Height H (Metric)		397.0mm
Depth D (imperial)		3.7"
Depth D (metric)		93.98mm
Material and Specifications		Material

855-04208



Material and Specifications	Material Shortcut	MET
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8538907080