

855-49200

# HellermannTyton

Article Number: 855-49200



Description: Rack Mount Fiber Enclosure-Unloaded, Accepts 3 LGX Adapter Panels, 1U, BK, 1/pkg

Base Data	
Local Order Number	FERM18S
Type	FERM18S
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> <li>• Removable front and rear covers provide easy access to cables.</li> <li>• Slide-out tray with easy-to-grip raised edge.</li> <li>• Cable management spools for effective slack management.</li> <li>• Optional splice trays to assist with cable splicing.</li> <li>• Panel positioning for easier patch cords access.</li> <li>• Round edge plastic fiber saddles for easier patch-cord routing.</li> <li>• Meet ANSI/TIA/EIA 568-C standards.</li> </ul>
Quantity Per	EA
Product Description	HellermannTyton's rack mount fiber enclosures are the ideal direct termination and splice solution of LAN applications capable of supporting up to 72 fibers. While offering easy-to-use front slide-out trays for effortless access to connections, enclosures are equipped with cable management and cable routing accessories to limit bend radius and add strain relief control. HellermannTyton's Rack Mount Fiber Enclosures easily fit into 19" or 23" racks.
Technical Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 3 Adapter Panels for Fiber Counts 18/24, 1U, BK
Short Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 3 LGX Adapter Panels, 1U, BK, 1/pkg
Product Dimensions	
Length L (Imperial)	12.14"
Length L (Metric)	308.4mm
Height in Units	1U
Width W (Imperial)	17.0"
Width W (Metric)	431.8mm
Height H (Imperial)	1.75"
Height H (Metric)	44.5mm
Depth D (imperial)	12.14"
Depth D (metric)	308.36mm

855-49200



Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8538907080
	Weight (imperial)	15.0lbs