

20 Amp Vertical Rackmount Outlet Strip *1589H-T Series*



Features

- Designed to have a low-profile our strips are just 1 5/8" wide by 1 3/8" high.
- Constructed of rugged light weight aluminum.
- Designed for a variety of applications:
 - Install in your server cabinets
 - Wall mount cabinets
 - Open frame racks
 - Or install horizontally above your work bench.
- Each outlet strip included a hardware mounting kit. Order P/N: **1585CLIP** for additional hardware kit.
- Receptacles are 1" square and are equally spaced over the length of the power strip.
- With on/off switch or pilot light and 20 Amp circuit breaker.
- Plug type available is a NEMA 5-15P straight blade.

Specifications

- CSA certified, Standards C22.2 (No. 21-95 and No. 42-99)
- UL listed, Standard UL1363 - file # E166039
- Heavy duty 12 gauge wire cord - 12/3 SJT for extreme temperature ranges and integral molded plug.
- Heavy-duty black receptacles rated for 20A, 125VAC service (NEMA 5-20R, Single T-Slot).
- Plug types available are NEMA 5-20P straight blade or NEMA L5-20P locking type.
- NOTE #1: Outlet strips can NOT be used between the front & rear panel rails of rack cabinets as they (and the equipment plugs) will interfere with mounted equipment and mounted accessories.
- NOTE #2: To properly use on rack cabinets, allow sufficient depth BEHIND the rear panel rails for vertically mounting to the amhul struts.

Accessories

- Vertical Outlet Strip Mounting Clip Kit

Part No. On-Off Switch	Part No. Pilot Light	Strip Length	Number of Outlets	Cord Length (ft)	Color	NEMA Plug Type
1589H18C1	1589T18C1	18	6	6	Natural	L5-20P
1589H18D1	1589T18D1	18	6	15	Natural	L5-20P
1589H18F1	1589T18F1	18	6	6	Natural	5-20P
1589H18G1	1589T18G1	18	6	15	Natural	5-20P
1589H24C1	1589T24C1	24	8	6	Natural	L5-20P
1589H24D1	1589T24D1	24	8	15	Natural	L5-20P

Part No. On-Off Switch	Part No. Pilot Light	Strip Length	Number of Outlets	Cord Length (ft)	Color	NEMA Plug Type
1589H24F1	1589T24F1	24	8	6	Natural	5-20P
1589H24G1	1589T24G1	24	8	15	Natural	5-20P
1589H36C1	1589T36C1	36	6	6	Natural	L5-20P
1589H36D1	1589T36D1	36	6	15	Natural	L5-20P
1589H36F1	1589T36F1	36	6	6	Natural	5-20P
1589H36G1	1589T36G1	36	6	15	Natural	5-20P
1589H42C1	1589T42C1	42	7	6	Natural	L5-20P
1589H42D1	1589T42D1	42	7	15	Natural	L5-20P
1589H42F1	1589T42F1	42	7	6	Natural	5-20P
1589H42G1	1589T42G1	42	7	15	Natural	5-20P
1589H48C1	1589T48C1	48	8	6	Natural	L5-20P
1589H48D1	1589T48D1	48	8	15	Natural	L5-20P
1589H48F1	1589T48F1	48	8	6	Natural	5-20P
1589H48G1	1589T48G1	48	8	15	Natural	5-20P
1589H48C116	1589T48C116	48	16	6	Natural	L5-20P
1589H48D116	1589T48D116	48	16	15	Natural	L5-20P
1589H48F116	1589T48F116	48	16	6	Natural	5-20P
1589H48G116	1589T48G116	48	16	15	Natural	5-20P
1589H60C1	1589T60C1	60	10	6	Natural	L5-20P
1589H60D1	1589T60D1	60	10	15	Natural	L5-20P
1589H60F1	1589T60F1	60	10	6	Natural	5-20P
1589H60G1	1589T60G1	60	10	15	Natural	5-20P
1589H70C1	1589T70C1	70	10	6	Natural	L5-20P
1589H70D1	1589T70D1	70	10	15	Natural	L5-20P
1589H70F1	1589T70F1	70	10	6	Natural	5-20P
1589H70G1	1589T70G1	70	10	15	Natural	5-20P
1589H70C124	1589T70C124	70	24	6	Natural	L5-20P
1589H70D124	1589T70D124	70	24	15	Natural	L5-20P
1589H70F124	1589T70F124	70	24	6	Natural	5-20P
1589H70G124	1589T70G124	70	24	15	Natural	5-20P
1589H77C1	1589T77C1	77	12	6	Natural	L5-20P
1589H77D1	1589T77D1	77	12	15	Natural	L5-20P
1589H77F1	1589T77F1	77	12	6	Natural	5-20P
1589H77G1	1589T77G1	77	12	15	Natural	5-20P

Data subject to change without notice