

Vertical Wall Mount Rack *VPB Series*

Heavy Duty 135 lbs Weight Capacity

Features



- Constructed in 14-gauge steel.
- 19" mounting EIA-310-D compliant rails with 10-32 tapped clip nuts.
- Horizontal or vertical equipment mounting.
- Rear cable access for cable management.
- Finished in textured black powder paint.
- Includes four (4) 10-32 black rack screws with washers and clip nuts per rack unit.
- Tested to nearly double the suggested load rating of 135 lbs (61 kg).
- RoHS Compliant.
- Manufactured in North America.



Gallery



Accessories

- Universal Rack Shelf
- Outlet Strips
- Hinged Acrylic Door Panel Cover
- 10-32 Mounting Screw and Clip Nut Combo-Pack

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
VPB192UBK	7.69	19.19	4.19	2U	3.50	19.00
VPB194UBK	7.69	19.19	7.69	4U	7.00	19.00
VPB196UBK	11.19	19.19	11.19	6U	10.50	19.00

