


## Knockdown Stacking Rack Cabinet *RCSC Series*

1,500 lbs Weight Capacity



Ideal for AV or IT/Server applications, the RCSC Rack Cabinet features a stacking design that allows for up to three (3) cabinets\* to be stacked atop each other. This Rack Cabinet is fully loaded and includes two (2) pairs of infinitely adjustable sliding EIA square-hole rails, punch-outs for cable entry and/or fan cooling and comes in a variety of sizes and depths.

The unique stacking feature enables your cabinet space to grow as your needs do \*Stack up-to three (3) 12U, two (2) 24U or one (1) of each cabinet atop each other using the required **RCSCBAY** baying kit. The 12U cabinet is a great starter cabinet for any small to medium sized business.

### Features

- Constructed in 16-gauge steel.
- Includes two (2) pair of 19" EIA-310-D compliant square-hole mounting rails with rack unit markings.
- Four (4) embosses are included with support for optional levelling feet or casters.
- Grounding studs provided on body.
- The top and bottom of the RCSC includes two (2) laser knockouts (per side) for cable-entry or fans (includes gasket strip material).
- Includes a laser knockout rear gland plate for floor-level cable entry.
- Finished in rugged black powder paint.
- Ships unassembled in a flat pack container for easy handling and shipping protection.



### Specifications

- Mounting rails are infinitely adjustable in depth and are fabricated of heavy duty 14-gauge steel, painted smooth black.
- Optional doors are available in solid, tinted acrylic with venting (see above-left) and high airflow vented.
  - Snap-in hinges can be mounted without having to bolt-on from inside the cabinet. In addition, the hinges can be mounted on the left or right.
- High airflow perforated doors for both front and rear of the cabinet are suggested for most server applications.
  - Perforated doors meet server manufacturer Free-Air-Ratio (FAR) requirements at 63%.
- For 36" depth cabinet side panels include cable entry knockouts.
- Tested to nearly double the suggested load rating of 1,500 lbs (680 kg).
- RoHS Compliant.
- Manufactured in North America.

### Gallery



## Accessories

- Universal Rack Shelf
- Rack Mount Locking Storage Drawer
- Sliding Keyboard Shelf
- Outlet Strips
- Adjustable Depth Cable Manager
- Horizontal Hinged Cable Manager
- Horizontal Steel Finger Cable Manager
- Caster Set
- Grill Fan Kits
- Adjustable Depth 4-Post Rack Mount Shelf
- Four Post Mounting Sliding Shelf
- 10-32 Mounting Screw and Cage Nut Combo-Pack
- Rack Unit Label
- Horizontal Lacing Strip
- Horizontal Ring Cable Manager
- Rack Panels
- Grounding
- Leveling Feet

| Part No.       | Overall Dimensions |       |       | Rack Units | Usable Mounting Dimensions |       |       |
|----------------|--------------------|-------|-------|------------|----------------------------|-------|-------|
|                | Height             | Width | Depth |            | Height                     | Width | Depth |
| RCSC1902124BK1 | 25.00              | 24.00 | 24.50 | 12U        | 21.00                      | 19.00 | 22.99 |
| RCSC1902131BK1 | 25.00              | 24.00 | 31.50 | 12U        | 21.00                      | 19.00 | 29.99 |
| RCSC1902136BK1 | 25.00              | 24.00 | 36.00 | 12U        | 21.00                      | 19.00 | 29.99 |
| RCSC1904224BK1 | 46.00              | 24.00 | 24.50 | 24U        | 42.00                      | 19.00 | 22.99 |
| RCSC1904231BK1 | 46.00              | 24.00 | 31.50 | 24U        | 42.00                      | 19.00 | 29.99 |
| RCSC1904236BK1 | 46.00              | 24.00 | 36.00 | 24U        | 42.00                      | 19.00 | 29.99 |

## Optional Doors

| Part No.       | Part No.       | Part No.           | Use with Cabinet Panel Height |            |
|----------------|----------------|--------------------|-------------------------------|------------|
| Solid Door     | Vented Door    | Vented Window Door | Units                         | Rack Units |
| RCSC19021SDBK1 | RCSC19021VDBK1 | RCSC19021WDBK1     | 21.00                         | 12U        |
| RCSC19042SDBK1 | RCSC19042VDBK1 | RCSC19042WDBK1     | 42.00                         | 24U        |

## RCSC Baying Kit

|          |         |
|----------|---------|
| Part No. | RCSCBAY |
|----------|---------|

*Data subject to change without notice*