

15 Amp Metered Horizontal Rackmount Outlet Strip *1582-AM Series*

Front or Rear Mounted Receptacles

Features

- Designed for power distribution for the front or the rear of the unit.
- 1U horizontal 19" rackmount installation.
- Available with lighted on/off switch or red pilot light to indicate power on.
- Available in black powder coat finish.



Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- Unit includes - easy to read 0.37" high, red LED ammeter (1.38" x 0.88" display).
- Digital ammeter accuracy +/- 0.1 Amps
- Units are cURus recognized to Standard UL1363 - file # E166039.



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit



Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		NEMA Type		Plug Blade Type	Cord Length	Rack Units
		Height	Width	Depth	Front	Rear	Outlet	Plug			
1582H6A1BKAM	1582T6A1BKAM	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	6 ft	1U
1582H6B1BKAM	1582T6B1BKAM	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	15 ft	1U
1583H6A1BKAM	1583T6A1BKAM	1.72	19.00	2.66	0	6	5-15R	5-15P	Straight	6 ft	1U
1583H6B1BKAM	1583T6B1BKAM	1.72	19.00	2.66	0	6	5-15R	5-15P	Straight	15 ft	1U

Data subject to change without notice

