



“X” Dimension: 3276 = .23” (5,8mm), 4513 = .48” (12,2mm)

### FEATURES:

- Threaded stud enables fast and easy mounting to panels.
- Solder turret allows wire attachment.
- Miniature banana plug spring features gold plated Beryllium Copper for long insertion life and low contact resistance.

Body: Brass, Gold Plated

Hex Nut: 4-40 Nut, Brass, Nickel Plated

### RATINGS:

Operating Voltage: 2500 VDC

Current: 5 Amperes Max.

### MATERIALS:

Miniature Banana Plug:

Spring – Beryllium Copper, Gold Plated

**ORDERING INFORMATION:** Model 3276 & 4513

Parts are packaged ten (10) per bag, unassembled.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA