


Enclosure population

For individual interior installation of the enclosures, system components from the Ripac range may be used (see from page 498).



Top covers

For Ripac Vario-Module

Standard version

Material:
Sheet steel, spray-finished

Colour:
RAL 7035

EMC version

Material:
Sheet steel, spray-finished
Contact points: Conductive

Width HP	Depth mm	Model No. VM standard		Model No. VM EMC	
		with vent holes	without vent holes	with vent holes	without vent holes
42	250.4	3982.941	3982.901	3981.941	3981.901
	310.4	3982.951	3982.911	3981.951	3981.911
63	250.4	3982.942	3982.902	3981.942	3981.902
	310.4	3982.952	3982.912	3981.952	3981.912
84	250.4	3982.940	3982.900	3981.940	3981.900
	310.4	3982.950	3982.910	3981.950	3981.910
	370.4	3982.960	3982.920	3981.960	3981.920
	430.4	3982.970	3982.930	3981.970	3981.930



Bottom covers

For Ripac Vario-Module

Standard version

Material:
Sheet steel, spray-finished

Colour:
RAL 7035

EMC version

Material:
Sheet steel, spray-finished
Contact points: Conductive

Width HP	Depth mm	Model No. VM standard		Model No. VM EMC	
		with vent holes	without vent holes	with vent holes	without vent holes
42	250.4	3982.741	3982.701	3981.741	3981.701
	310.4	3982.751	3982.711	3981.751	3981.711
63	250.4	3982.742	3982.702	3981.742	3981.702
	310.4	3982.752	3982.712	3981.752	3981.712
84	250.4	3982.740	3982.700	3981.740	3981.700
	310.4	3982.750	3982.710	3981.750	3981.710
	370.4	3982.760	3982.720	3981.760	3981.720
	430.4	3982.770	3982.730	3981.770	3981.730




Feet

with fold-out support stand.
Load capacity up to 20 kg.

Material:
Plastic

Colour:
RAL 7035

Packs of	Model No. VM
2	3919.000



Mounting plate

For mounting heavy components.

Material:
Aluminium

Supply includes:
Assembly parts.

Width HP	Depth mm	Packs of	Model No. VM
42	220	1	3982.370
63	250	1	3982.380
84	250	1	3982.390