

Flush Extension Speaker Range

Product Overview

Elmdene's new range of flush extension speakers have been designed to be used with all common Intruder panels. Offering a more aesthetic look compared to standard types, they are available in two finishes:

- White Plastic
- Brushed Stainless Steel

Offered in a single gang format they will fit either a flush mounting box or a standard surface box.

Both plates are supplied with an optional rear tamper switch, monitoring for plate removal if required. Speakers are rated at 16 Ohms impedance making them compatible with all common control panels.

The devices use modern, stylish face plates which can be screen printed with a company logo if required (MOQ applies).

Features

- Flush or surface mount
- Single gang size (86mm x 86mm)
- White plastic or brushed steel options
- Provided with 16 Ohm speaker
- Tampered
- Provided with plate screws (30mm length)
- Aesthetically pleasing design
- Environmental class II
- Provided with termination blocks for speaker & tamper connections
- Screen printing available on all models
- 3 year warranty



Flush Extension Speaker Range

Part Numbers

Part no	Description
EXTSP-16T-SS	Flush Mounted Stainless Steel 16 Ohm Extension Speaker - Tampered
EXTSP-16T-W	Flush Mounted White Plastic 16 Ohm Extension Speaker - Tampered

Part no	Accessory
EXTSP-BOX-SS	32mm Surface Box - Brushed Steel

Technical Information

16 Ohm Impedance

Correct tamper operation requires a mounting box depth of 25mm to 35mm

Approvals & Certification

Suitable for use in Grade 3 / PD6662 systems
CE Approval

Product Dimensions

H x W x D: 87mm x 87mm x 20mm

