

Industrial Connectivity and Control Products

Accessories

Accessories

Hubbell offers the broadest line and widest choice of cord connectors to complete your installation of Mini-Quick Control Connectors. Hubbell Cord Connectors feature our patented GOTCHA® Ring technology to prevent friction and provide superior strain relief. Our Cord Connectors are IP66 and come in a variety of materials to meet your environmental needs.



IP 66*
Suitability

Machined Zinc Plated Steel



Machined Aluminum



Nylon



Cord Connectors- Straight Male

Cord Range	NPT Hub Size	Form Size	Zinc Plated Steel	Machined Aluminum	Nylon Gray	Nylon Black	Metal Clad O-Ring
.19" - .25"	1/2"	F2	SHC1021ZP	SHC1021	SHC1021CR	SHC2021CR	20509001
.25" - .38"	1/2"	F2	SHC1022ZP	SHC1022	SHC1022CR	SHC2022CR	20509001
.38" - .50"	1/2"	F2	SHC1023ZP	SHC1023	SHC1023CR	SHC2023CR	20509001
.50" - .63"	1/2"	F2	SHC1024ZP	SHC1024	SHC1024CR	SHC2024CR	20509001
.63" - .75"	1/2"	F2	SHC1027ZP	SHC1027	-	-	20509001



Low Profile Cord Connectors

Cord Range	NPT Hub Size	(mm)	Gray Nylon	Black Nylon	Natural Nylon Locknuts
.18" - .31"	3/8"	(4.6-7.9)	SEC38GA	SEC38BA	31622002LPK50
.17" - .45"	1/2"	(4.3-11.4)	SEC50GA	SEC50BA	31622003LPK50
.45" - .71"	3/4"	(11.4-18.0)	SEC75GA	SEC75BA	31622007LPK50
.59" - 1.00"	1"	(15.0-25.4)	SEC100GA	SEC100BA	31622008LPK50

Notes: See Section T for the full line of Hubbell premium cord connectors. Catalog numbers with PK50 suffix are packed 50 per carton.