

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191210009
Status: Active
Overview: Solderless Terminals
Description: InsulKrimp™ Flanged Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-009-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)
[Product Specification PS-19902-013-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


Agency Certification
CSA LR18689
UL E32244

General
Product Family Ring and Spade Terminals
Series 19121
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Solderless Terminals
Product Name InsulKrimp™
Type Spade
UPC 800753095298

Physical
Barrel Type Closed
Flammability 94V-0
Insulation PVC
Material - Plating Mating Tin
Net Weight 0.608/g
Packaging Type Bag
Stud Size 10 (M5)
Wire Insulation Diameter 3.68mm
Wire Size AWG 18, 20, 22
Wire Size mm² 0.25-1.50

Material Info
Engineering Number AA-215-10X

Reference - Drawing Numbers
Product Specification PS-19902-009-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19121-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per -ED/01/2017 (12 January 2017) Halogen-Free Status Not Low-Halogen	China RoHS
---	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19121](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION