



HY434/12 NYLP

12 pole natural polyamide PA6.6 wire protected pillar terminal block 12mm pitch 41a 450v



SPECIFICATION

Number of Poles	12
Terminal Material	OT58 nickel plated
Terminal Type	Wire Protected
Body Material	Polyamide PA6.6
Colour	Natural
Glow Wire Resistance Test Temp	GWIT775°C (EN60695-2-13)
Max Conductor Size (Sq mm)	6
Max Current (A)	41
Max Voltage (V)	450
Working Temperature	110
Pitch (mm)	12
Height (mm)	20
Width (mm)	23.1
Length (mm)	139.6
Diameter (mm)	3.2
Flammability Rating	UL94V2 and GWIT775°C
Terminal Screw Material	White zinc plated steel
Wire Protection Material	Stainless steel