

166-90125

Article Number: 166-90125



Description: HelaGuard Non-Metallic IP65 Fitting, 45-Elbow, NPT Thread, 0.50" Dia, PA66, Black, 10/pkg

Base Data	
Local Order Number	166-90125
Type	PSR050-45-0500
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Twist-on installation makes future access fast and easy. • Internal spigot design helps ease threading of fitting onto conduit. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP65 rating for protection against wind, dirt and low pressure jets of water from all directions.
Quantity Per	bag
Product Description	Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.
Short Description	HelaGuard Non-Metallic IP65 Fitting, 45-Elbow, NPT Thread, 0.50" Dia, PA66, Black, 10/pkg
Product Dimensions	
Length L (Imperial)	2.36"
Length L (Metric)	60mm
Bore Diameter (Imperial)	0.57"
Bore Diameter (Metric)	14.5mm
Clearance Hole Diameter (Imperial)	0.827"
Clearance Hole Diameter (Metric)	21mm
Thread Length (Imperial)	0.51"
Trade Size	1/2 "
Outside Diameter D (imperial)	1.30"
Outside Diameter D (metric)	33mm
Nominal Diameter (Imperial)	1/2"
Nominal Diameter (Metric)	20mm
Thread Length (metric)	13mm

166-90125



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987