

166-90448



Article Number: 166-90448

Description: HelaGuard Accessories, Sealing Washer, M25-3/4", Polyester Elastomer, Blue, 10/pkg

Base Data	Local Order Number	RSW25-BU
	Type	RSW075
	Color	Blue (BU)
	Features and benefits	<ul style="list-style-type: none"> • Polyester elastomer washer provides ingress protection against moisture and is oil resistant. • Small "pips" in bore retain washer onto metric threaded fittings. • Ribs on both sides of washer enhances sealing performance.
	Quantity Per	pack
	Product Description	Face sealing washer affixed between metric threaded fitting and entry wall surface to achieve IP66, IP67, IP68 and IP69 levels of ingress protection. Hardness 33 Shore D. Self-extinguishing and halogen free.
	Technical Description	Manufacturer Reference Number: RSW25-BU
	Short Description	HelaGuard Accessories, Sealing Washer, M25-3/4", Polyester Elastomer, Blue, 10/pkg
	Product Dimensions	Inner Diameter D (Imperial)
Inner Diameter D (metric)		25.0mm
Outside Diameter D (imperial)		1.34"
Outside Diameter D (metric)		34.0mm
Nominal Diameter (Imperial)		3/4"
Nominal Diameter (Metric)		25.0mm
Thickness T (Imperial)		0.06"
Thickness T (Metric)		1.6mm
Material and Specifications	Material	Thermoplastic Elastomer (TPE)
	Material Shortcut	TPE

166-90448



Material and Specifications	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	4016930000