

166-90220

Article Number: 166-90220

Description: HelaGuard SR PVC Tubing, Smooth Bore, Spiral Cover, Std Wt, 0.38" Dia, Bk, 100 ft/Std. Reel



Base Data	
Local Order Number	166-90220
Type	PSR0380
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> <li>• Spiral reinforced construction provides protection from crushing yet remains extremely flexible.</li> <li>• Lightweight, easy-to-use material reduces installation time and labor costs.</li> <li>• Material stands up to vibration and limited torsional movement without creation of stress points or cracks.</li> <li>• Smooth inside bore protects wires and eases insertion of wire bundles.</li> <li>• UV resistant; suitable for use in outdoor applications.</li> </ul>
Quantity Per	reel
Product Description	A lightweight tubing with a smooth inside bore, made of a spiral reinforced PVC material that provides high flexibility. This tubing is well-suited for protecting wire and cable bundles in extremely tight spaces. UV resistant. Use with HelaGuard Non-Metallic Compression Fittings to create an enclosed system.
Short Description	HelaGuard SR PVC Tubing, Smooth Bore, Spiral Cover, Std Wt, 0.38" Dia, Bk, 100 ft/Std. Reel
Product Dimensions	
Length L (Imperial)	100.0ft
Length L (Metric)	30.5m
Inner Diameter D (Imperial)	0.48"
Inner Diameter D (metric)	12mm
Trade Size	3/8 "
Outside Diameter D (imperial)	0.65"
Outside Diameter D (metric)	16.5mm
Nominal Diameter (Imperial)	3/8"
Nominal Diameter (Metric)	16mm
Inside Bend Radius (Imperial)	0.99"
Inside Bend Radius (Metric)	25mm

166-90220



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	self-extinguishing according to EN IEC 61386
	Halogenfree	No
	Operating Temperature	-4°F to +158°F (-20°C to +70°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.5m
	Customs Number(Schedule B)	3926909987