

## LED Driver - Constant Voltage Mains Dimmable 150W



### Features:

- Compact design measuring 260 x 78.3 x 45mm
- AC input 200-240vac 50Hz
- Short circuit, Over voltage and Over power Protections
- Cooling by free air convection for high reliability
- 100% ageing test on full load
- Compliance to lighting safety standards
- Available in both 12vdc and 24vdc constant voltage options
- Dimming mode: Triac (Mains dimmable)
- Efficiency 85%
- High Power Factor: Up to 0.98
- Supports both leading edge (Triac) and Trailing edge (ELV) Dimming
- Constant voltage single output
- Weight: 842g

Model	Voltage Output	Load	Maximum Output Current	Dimensions
PAX12150TD-B	12vdc	0—150W	12.5A	260 x 78.3 x 45mm
PAX24150TD-B	24vdc	0-150W	6.2A	260 x 78.3 x 45mm

This range of LED driver is manufactured and approved to lighting standards IEC61347-1 and also IEC61347-2-13. It provides a constant voltage regulated output at up to 150 Watts. 2 models are available as either 12vdc or 24vdc. Suitable for use indoor use only, rated to IP20. We recommend a good quality dimmer switch is used for best results, such as the Varilight Pro series