

Benchtop Shot Meter with Vacuum Only



◀◀ previous print close next ▶▶

Product Details

Catalog No.	KDS808
UPC Code	037103173706
Input voltage	115 V 230 V
Output Voltage	24 V
Air Input/Output	0-100 psi
Vacuum	0-18 in. Hg
Timer Ranger	No Timer
Packaging	Industrial Box/Carton
Literature	5506901A.pdf
Low Res. Image	KDS808_100.jpg
High Res. Image	KDS808_300.jpg
Operating Ins.	KDS808_834A_824A_OI_PL.pdf
Parts List	KDS808_834A_824A_OI_PL.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- **Basic low cost system**
- **Easy to set up and operate, "Eyeball" accuracy**
- **Electrically actuated foot pedal**
- **Vacuum feature prevents dripping**
- **0 - 100 PSI regulators and gauges with locking ring**
- **Benchtop unit; easy reading of dials, adjustment of air pressure, vacuum**
- **Low voltage unit, slide switch easily changes unit from 115 to 230 volts**
- **Order syringe adapters, kits and other accessories separately**