

## Weller

### Weller Soldering Ironw/LED's (25 Watt)

◀◀ previous print close next ▶▶

#### Product Details

<b>Catalog No.</b>	<b>SP25NUS</b>
<b>UPC Code</b>	<b>037103266880</b>
<b>Type</b>	<b>25W</b>
<b>Wattage</b>	<b>750°F / 400°C</b>
<b>Temperature Range</b>	<b>6 ft.</b>
<b>Cord Length</b>	<b>MT1 0.125" (3mm) Conical</b>
<b>Components Supplied</b>	<b>Peg Hook Retail/Packaging</b>
<b>Tech. Spec.</b>	<b><u><a href="#">Solder Safety Warnings.pdf</a></u></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

#### Package Details (Dimensions)

Email this Page

#### Product Features:

- **Three LED lights for limited application shadowing**
- **Round Co-molded soft grip handle design for easy tip positioning**
- **Triangular handle area for maximum tip control**
- **Stainless steel barrel and heater**
- **UL listed - cUL version available**
- **Excellent quality consumer iron 8 1/4" (210mm) long**
- **Light duty iron, (25watts) for joining 16 AWG wire or smaller**
- **Use on small electrical/electronic assemblies, appliance repair, etc.**
- **IMPORTANT: Use only Weller® tips**