

F0134000KF – DREMEL® 4000 Platinum Edition

| | |
|--|---------------|
| Material number | F0134000KF |
| EAN | 8710364057955 |
| 128 high quality Dremel accessories | ✓ |
| Aluminum carry case | ✓ |
| Cutting Guide attachment 565 | ✓ |
| Detailer's Grip attachment 577 | ✓ |
| Dremel 4000 | ✓ |
| Flexshaft attachment 225 | ✓ |
| Instruction manual | ✓ |
| Line & Circle Cutter attachment 678 | ✓ |
| Right Angel attachment 575 | ✓ |
| Shaping Platform attachment 576 | ✓ |



Technical data

Technical specifications

| | |
|-------------------------------|-----------------------------|
| Rated power input | 175 W |
| Voltage | 230 V |
| Weight | 0,66 kg |
| Length | 23 cm |
| Width | 4.1 cm |
| Depth | 4.3 cm |
| No load speed | 5.000 - 35.000 1/min |
| Battery technology | n.a. |
| Speed setting | Fully Variable |
| Accessory quick change system | EZ Twist |
| Sound pressure | 77,9 dB(A) |
| Sound power | 88,9 dB(A) |
| Vibration | 2,6 - 11,4 m/s ² |

E-Dealers

Reasons-to-buy (e-dealer)

Platinum Edition: the most versatile corded Multi-Tool kit with 128 accessories and 6 attachments included. Strong and dynamic Multi-Tool for everyday use Experience maximum control and precision with the most variable rotary speed (5.000 – 35.000) Packed in a sturdy aluminum tool case for safe transportation and easy storage 2 year warranty

Packaging dimensions

| | |
|--------------------|---------|
| Product box length | 24.3 cm |
| Product box height | 23.6 cm |
| Product box width | 43.7 cm |
| Gross weight | 6,00 kg |

Sales information

Benefits

- The Dremel 4000 Platinum Edition is the ultimate Dremel Multi-Tool kit. Besides the top of the line Dremel 4000 with EZ Twist Nose Cap you get 6 useful attachments and 128 genuine Dremel accessories all packed in a high quality aluminum tool case. With this supreme kit even the most demanding craftsman will be satisfied.