

### THB.381.M2A

Micro Socket M11 IP68 10A 400V 1 cable entry



#### SPECIFICATION

|                        |  |
|------------------------|--|
| Type                   | Socket                                   |
| Cable Entries          | 1  |
| Number of Poles        | 2  |
| Terminal Type          | Silver-plated brass (zinc-plated screws) |
| Body Material          | PA66 GF UL94 V0                          |
| IP Rating              | 68                                       |
| Max Current (A)        | 10                                       |
| Max Voltage (V)        | 400                                      |
| Minimum Temp Rating °C | -40                                      |
| Max Temp Rating °C     | 125                                      |
| Fixing System          | Cable                                    |
| Temperature "T" Rating | T125                                     |