



Main

Disconnecter device type	Fusible disconnect switch
Enclosure type	Enclosure standard environment indoor
Series name	Heavy duty

Complementary

[In] rated current	30 A
AWG gauge	AWG 14...AWG 6 copper AWG 12...AWG 6 aluminium
Device mounting	Surface
Electrical connection	Lugs
Enclosure material	Steel
Interlocking type	Without electrical interlock
Number of poles	3
Permissible voltage	<= 600 V
Short circuit protection	200 kA R or J 10 kA H or K
Switch function	TPST
Wiring configuration	Without neutral

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed

Ordering and shipping details

Category	00160 - DE1 MISC
----------	------------------

GTIN	00785901076988
Nbr. of units in pkg.	1
Package weight(Lbs)	9
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------