

Electronic housing - ME 22,5 UTG/FE GN - 2907101

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component housing without vents, Lower part, Cross connection: without bus connector, Color: green, Width: 22.5 mm, Constructional height: 114.5 mm

Why buy this product

- Item is from the ME product range
- Tool-free mounting
- Available in overall widths from 12.5 mm to 90 mm, modular extension is possible
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail
- Optional bus connector that is either integrated or mounted on the DIN rail

Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 017918 126599
GTIN	4017918126599
Weight per Piece (excluding packing)	33.170 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color	green

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Electronic housing - ME 22,5 UTG/FE GN - 2907101

Technical data

Dimensions

Length	99 mm
Constructional height	114.5 mm
Width	22.5 mm

Technical data

Flammability rating according to UL 94	V0
Power dissipation without gap	5.5 W
Power dissipation with 20 mm gap	9.6 W
Number of positions	16
	24

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Electronic housing - ME 22,5 UTG/FE GN - 2907101

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868

Accessories

Accessories

Mounting material

Electronic housing - ME LPZS - 2906911



Component housing

Necessary add-on products

Electronic housing - ME 22,5 OT-MSTBO SET - 2907444

Component housing, Upper part, Color: green, Width: 22.5 mm, Constructional height: 38.5 mm



Electronic housing - ME 22,5 OT-MSTBO GN - 2907169



Component housing, Upper part, Color: green, Width: 22.5 mm, Constructional height: 38.5 mm

Electronic housing - ME 22,5 UTG/FE GN - 2907101

Accessories

Electronic housing - ME 22,5 OT-1MSTBO GN - 2709558



Component housing, Upper part, Color: green, Width: 22.5 mm, Constructional height: 38.5 mm

Electronic housing - ME 22,5 OT-MKDSO SET - 2907473



Component housing, Upper part, Color: green, Width: 22.5 mm, Constructional height: 38.5 mm

Electronic housing - ME 22,5 OT-MKDSO GN - 2907172



Component housing, Upper part, Color: green, Width: 22.5 mm, Constructional height: 38.5 mm
