

# Cable gland - HC-B-G-M20-PLRBK - 1407669

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



EVO plastic cable gland with bayonet locking, for housing series B, size M20, cable diameter: 7 ... 13 mm

## Product Description

Plastic cable gland



## Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 776370
GTIN	4046356776370
Weight per Piece (excluding packing)	32.340 g
Custom tariff number	39269097
Country of origin	Poland

## Technical data

### Dimensions

Wrench size, union nut	22 mm
External cable diameter	7 mm ... 13 mm

### Ambient conditions

Degree of protection	IP66
	12 (UL 50)
Ambient temperature (operation)	-40 °C ... 100 °C

### General

Type of the screw connection	M20
No. of conductors	1
Material	PA
Cable gland material	PA
Material, pressure screw	PA

# Cable gland - HC-B-G-M20-PLRBK - 1407669

## Technical data

### General


Seal material	NBR
Cable seal material	NBR
Shielded	No
Thread type on connection side	Bayonet B plastic
Tightening torque, union nut	5.00 Nm
Flammability rating according to UL 94	V0 (Seal)
	V2 (Housing)
Assembly instructions	Bayonet locking max. 3x can be removed

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Dimensional drawing



Dimensional drawing

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27143424
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441
ETIM 6.0	EC000441

# Cable gland - HC-B-G-M20-PLRBK - 1407669

## Classifications

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	39121311

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

### Approval details

EAC		7500651.22.01.00246
-----	--	---------------------

## Accessories

### Accessories

Corrugated pipe screw connection

Corrugated tube screw connection - WP-GR HF CTA M20 BK - 3241220



Corrugated pipe adapter, with M20 internal thread, straight, black, IP66, for connecting corrugated pipes to HEAVYCON EVO plastic cable glands or ADVANCE plastic housing.